

GRAB BARS AND ACCESORIES FOR A BARRIER-FREE WASHROOM

MEDIEPOXI / MEDINOX

130° angled grab bar



General description

- Stainless steel 130° angled grab bar made of a 32 mm diameter tube and designed to provide relief and assistance around the bathroom.
- Stylish design making this grab bar ideal for the bathroom and other rooms in the house.
- Unique angled design provides support no matter the position.
- Durable, secure and stable, these grab bars provides confidence and stability when getting in or out of the bath or shower.
- 32mm diameter bar for easier gripping.
- Concealed fixings thanks to their beautiful snap flange covers.
- Optionally, they have a kit to avoid electrical conductivity, code KA0010 for grab bars BA2130 and BA2130B or code KA0020 for grab bars BA0130C and BA0130CS.
- Stainless steel nuts and bolts for masonry walls included.


Components and materials


- BA2130: grab bar made of AISI 201 stainless steel tube, white epoxy finish.
- BA2130B: grab bar made of AISI 201 stainless steel tube, matte black epoxy finish.
- BA0130C: grab bar made of AISI 304 stainless steel tube, bright finish.
- BA0130CS: grab bar made of AISI 304 stainless steel tube, satin finish.
- TUBING: made of 32 mm diameter tube, seamless construction. The bending process guarantees the uniformity of the diameter along the bends.
- CONCEALED WALL BRACKET: two units made of steel (BA0130) or stainless steel AISI 304 (BA0130C and BA0130CS), 3 mm thick. Incorporates three (BA0130) or two (BA0130C and BA0130CS) screws holes for wall mounting.
- SNAP FLANGE COVER: two units made of white Polypropylene, 1.5 mm thick and Ø 85 mm (BA0130) or stainless steel AISI 304, 0.8 mm thick and Ø 82 mm (BA0130C and BA0130CS). Each cover snaps over mounting flange to conceal mounting screws.

Technical specifications

Bar diameter	Ø 32 mm
Wall bracket thickness	3.0 mm

Dimensions






Ref. / Code	L(X)	Ø (Y)	Material	Acabado Finish
BA2130	625mm	85mm	Acero Inox Stainless steel	Epoxi blanco White epoxy
BA2130B	625mm	85mm		Epoxi negro Black epoxy
BA0130C	622mm	82mm		Brillante Bright
BA0130CS	622mm	82mm		Satinado Satin


Dimensions: ± 4%

MOUNTING TEMPLATE


Fix the grab bar to the wall through the 3 or 2 holes of the wall brackets to the wall, using the screws provided and taking into account the distances of the points indicated by an "S" in the following figure:


BA2130 and BA2130B





BA0130C and BA0130CS





Mediclinics is not responsible for corrosion that may appear on the bars caused by abrasion on the anchorage points because of an improper installation.

